

MT Standard Series



MT1PUL



MT2UL



MT3ULBL



MV2ULAF

Dispense frozen cappuccino, fruit slush, smoothies, sorbet, & much more!

Industry Leading Features

The MT Standard Series includes all the features found on the MT Mini Series plus the following additions:

- **Dual Surface Freezing Chamber** – Freezes product on the outside & inside of the cylinder as dual augers keep the product surface level & free of ice blocks.
- **Reversible Lid With lighted Graphics** – Provides maximum merchandising for your frozen drink sales.
- **Filter Indicator Light** – When lit indicates that the filter needs to be cleaned, eliminate unnecessary service calls!

Manual Fill Models

Model	MT1PUL	MT1PUL BL	MT2UL	MT2UL BL	MT3UL	MT3UL BL
Finish	SS	Black	SS	Black	SS	Black
# Of Bowls	1	1	2	2	3	3
Bowl Capacity	2½ gal.	2½ gal.	2½ gal.	2½ gal.	2½ gal.	2½ gal.
HP	¼	¼	½	½	¾	¾
Width	11½"	11½"	14¼"	14¼"	21"	21"
Depth	18½"	18½"	18½"	18½"	18½"	18½"
Height	27¾"	27¾"	27¾"	27¾"	27¾"	27¾"
Ship Weight	67 lbs.	67 lbs.	95 lbs.	95 lbs.	125 lbs.	125 lbs.

Auto Fill Ready Models*

Model	MT2ULAF	MT2ULAFBL	MV2ULAF	MT3ULAF
Finish	SS	Black	SS	SS
# Of Bowls	2	2	2	3
Bowl Capacity	2½ gal.	2½ gal.	2½ gal.	2½ gal.
HP	½	½	(2)½	¾
Width	14¼"	14¼"	14¼"	21"
Depth	18½"	18½"	18½"	18½"
Height	27¾"	27¾"	35¾"	27¾"
Ship Weight	97 lbs.	97 lbs.	148 lbs.	127 lbs.

Electrical: Line cord included, MT1P & MT2 = 120V, 1.7KW, 15A, MT3 & MV2 = 120V, 2.3KW, 20A. SS: Stainless steel, stainless dispensers come standard with light gray tops & drip trays. *For use with liquid bag-in-the-box apparatus.

Patented Magnetic Drive System

Magnetic Drive Slippage System.


- The Auger Motor Turns Magnetically Eliminating The Need For Front Or Rear Seals.
- Auger Fits Securely Over The Outside Of The Magnetic Drive System, Turning Via A Series Of Magnets.
- The Granita Product Is Encapsulated Inside The Bowl.
- Eliminates Damage To The Auger Motor If Product Freeze-Up Occurs.
- This System Lowers Maintenance Costs & Decreases Auger Motor Burnout.

** Standard & Giant Series only, the Mini Series uses a solid single sided chamber.

Dual Surface Freezing Chamber**



Cut-Away View



Cut-Away View